



UGRGF Series 20A, 125V GFI Protected Receptacle, 3/4" Dead End

By Killark
Catalog # [UGRGF108](#)

20A, 125V GFI Protected Receptacle, 3/4" Dead End



Features

- Factory Sealed.
- Test and Reset push buttons are provided on cover assembly.
- Includes new GFCI to meet latest UL943 GFCI standards revisions.
- Exterior gasket provides NEMA 3 weatherproof protection.
- Ground boss for grounding in the splice box.
- Color coded wiring and stainless steel cover bolts.
- Receptacle used is UGR0-20231QW.
- Unit should be tested monthly.

Specifications

Hazardous Rating(s)	• Class 1, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 7(C, D), 9(F, G)
CSA File Number	LR11714

Buy America(n) Qualified

BABA Compliant (All status valid till December 2025)

Conductor

Number Of Wires	3
Number Of Poles	2

Current

Amperage Rating	20
Voltage Rating	125 VAC

Dimensions

Hub Size	3/4"
Weight	7.5 lb.

General

Series	UGRGF Series
UPC	783936784533

Product Assets

[Catalog \[English\]](#)