



UGRP Series 20A 125V Acceptor Panel Receptacles with Breech-Lock Cap, Quick-Wire

By Killark
Catalog # [UGRP-20231BQW](#)

20A 125V Acceptor Panel Receptacles with Breech-Lock Cap, Quick-Wire

Features

- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch – requires Hazardous Rated NEMA-Bladed Plug for operation

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)



Buy America(n) Qualified	Contact Manufacturer
Conductor	
Number Of Wires	3
Number Of Poles	2
Current	
Amperage Rating	20 A
General	
Receptacle Type	Delayed Action
Type	Straight Blade
Series	UGRP
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936125626
Logistics	
Factory Sealed	Factory Sealed
Product Assets	
Catalog [English]	