



UGRS Series 20A 125V Square Receptacle with Breech-Lock Cap - 1" E-TYPE

By Killark
Catalog # [UGRS-20231BE3](#)

20A 125V Square Receptacle with Breech-Lock Cap - 1" E-TYPE



Features

- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch - requires Hazardous Rated NEMA-Bladed Plug for operation
- Rotateable Design allows for installation flexibility

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups B, C, D • Class I, Zone 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	3
Number Of Poles	2

Configuration

Hub Pattern	Dead-End
-------------	----------

Current

Amperage Rating	20 A
Frequency Rating	50/60 Hz
Voltage Rating	120-277 VAC

Dimensions

Hub Size	1"
----------	----

General

Receptacle Type	Delayed Action
Type	Straight Blade
Series	UGRS Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936124599

Logistics

Factory Sealed	Factory Sealed
Carton Quantity	1

Operational

Operating Temperature Range Celcius	-40°C to 40°C
Operating Temperature Celcius Max	40
Operating Temperature Celcius Min	-40 °C

Product Assets

[Catalog \[English\]](#)