



UGRS Series 20A 125V Square Receptacle with Flip Lid - 3/ 4" D-TYPE

By Killark
Catalog # [UGRS-20231FD2](#)

20A 125V Square Receptacle with Flip Lid - 3/ 4" D-TYPE

Features

- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch - requires Hazardous Rated NEMA-Bladed Plug for operation
- Rotateable Design allows for installation flexibility

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups B, C, D • Class I, Zone 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	3
-----------------	---



Number Of Poles	2
-----------------	---

Configuration

Hub Pattern	Angled Feed-Thru
-------------	------------------

Current

Current Rating	100 A
Amperage Rating	20 A

Dimensions

Hub Size	3/4"
----------	------

General

Receptacle Type	Delayed Action
Type	Straight Blade
Series	UGRS Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936125855

Logistics

Factory Sealed	Factory Sealed
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)