



# UGRS Series 20A 125V Square Receptacle with Flip Lid - 1/ 2" E-TYPE

By Killark  
Catalog # [UGRS-20231FE1](#)

20A 125V Square Receptacle with Flip Lid - 1/ 2" E-TYPE

## Features

- Available with Exclusive Breech-Lock Lid
- Patented lid notch allows for screwdriver, etc. to hold open lid for easier, two-hand installation.
- Factory Sealed Construction
- Copper-free aluminum (less than 4/10 of 1%) alloy resists corrosion
- Electrostatically applied and baked powder epoxy/polyester finish
- Dead Front Construction with Integral Switch - requires Hazardous Rated NEMA-Bladed Plug for operation
- Rotateable Design allows for installation flexibility

## Specifications

|                          |                                                                                                                                                                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups B, C, D</li><li>• Class I, Zone 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                              |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                              |

## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 3 |
|-----------------|---|



|                 |   |
|-----------------|---|
| Number Of Poles | 2 |
|-----------------|---|

## Configuration

|             |          |
|-------------|----------|
| Hub Pattern | Dead-End |
|-------------|----------|

## Current

|                 |       |
|-----------------|-------|
| Current Rating  | 100 A |
| Amperage Rating | 20 A  |

## Dimensions

|          |      |
|----------|------|
| Hub Size | 1/2" |
|----------|------|

## General

|                 |                                              |
|-----------------|----------------------------------------------|
| Receptacle Type | Delayed Action                               |
| Type            | Straight Blade                               |
| Series          | UGRS Series                                  |
| Material        | Aluminum, Copper Free (less than 4/10 of 1%) |
| UPC             | 783936126098                                 |

## Logistics

|                 |                |
|-----------------|----------------|
| Factory Sealed  | Factory Sealed |
| Carton Quantity | 1              |

## Product Assets

[Catalog \[English\]](#)