



UNF100 - Hazardous Location Union - Zinc Plated Steel - 1" Female/Female

By Killark
Catalog # UNF100

Hazardous Location Union - Zinc Plated Steel - 1" Female/Female



Features

- Unique design offers a compact size for lighter weight and smaller profile for critical clearances with equipment
- Extruded bar stock construction provides superior threads over sand cast and provides twice the tensile strength
- Uniform design across all sizes for aesthetic and robust appeal
- Male to Female union has nonremovable nipple to ensure tight seal with union and pipe/equipment
- Made in the USA

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups A, B, C, D • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	4

Buy America(n) Qualified

Contact Manufacturer

Dimensions

Hex Size	1.69 in
Hub Size	1"
Weight	0.4 lb.
Length	1.81 in
Diameter	1.75 in

General

Type	Female/Female Union
Series	UNF Series
Material	12L14 Steel
Finish Type	Zinc Plated
UPC	783936184067
Color	Silver

Product Assets

[Catalog \[English\]](#)