



UNYO-EX - UN Series - Iron ATEX And IECEx Certified Union - Male/Female - Hub Size 4 Inch

By Killark
Catalog # UNYO-EX

UN Series - Iron ATEX And IECEx Certified Union - Male/Female - Hub Size 4 Inch

Features

- Threaded for rigid conduit or IMC
- Tapered threads (NPT)
- Strong and durable construction
- Certified QUAD LISTED

Application

UNY unions are used to connect two pieces of conduit or attach conduit to junction boxes, fittings, or devices. Permits removal of equipment without turning or removal of conduit.

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
IECEx File Number	IECExITS09.0024U
EU RoHS Indicator	Contact Manufacturer



Buy America(n) Qualified ATEX File Number	Contact Manufacturer ITS09ATEX16417U
---	--------------------------------------

Dimensions

Gross Weight with Packaging	12
Hub Size	4"
Width	7 in
Height	7 in
Length	6 in
Dimensions	6 in x 7 in x 7 in

General

Type	Male to Female Union
Series	UNY Series
Material	Iron
Finish Type	Zinc Plated
UPC	783936072210
Color	Glossy gray

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)