



# VBQ Series Hazardous Interlocked Receptacle - Cutler Hammer - FD Series 60A Breaker 3P 4W

By Killark  
Catalog # [VBQ6034CH60](#)

Cutler-Hammer - FD Series 60A Receptacle 60A Breaker 3W4P

## Features

- Plug Interlock Mechanism for Dead-Front construction. Switch cannot be turned “ON” without fully inserted plug. Plug cannot be removed with switch in “ON” position
- Ground Fault Options Available
- Spacious wiring room that meets NEC wire bending requirements.
- Adjustable mounting lugs
- Quick Release Cover Bolts with Triple Leads for faster removal
- Electrostatically applied polyester/epoxy finish
- Breaker Handle has provisions for locking “ON” or “OFF” with up to three Padlocks

## Specifications

|                          |                                                                                                                                                                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s)      | <ul style="list-style-type: none"><li>• Class I, Division 2, Groups B, C, D</li><li>• Class I, Zone 2, Groups IIB+H2, IIA</li><li>• Class II, Divisions 1 &amp; 2, Groups F, G</li><li>• Class III, Divisions 1 &amp; 2</li></ul> |
| EU RoHS Indicator        | Contact Manufacturer                                                                                                                                                                                                              |
| Nema Rating              | 7 (C, D)                                                                                                                                                                                                                          |
| Buy America(n) Qualified | Contact Manufacturer                                                                                                                                                                                                              |



## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 4 |
| Number Of Poles | 3 |

## Configuration

|             |          |
|-------------|----------|
| Hub Pattern | Dead-End |
|-------------|----------|

## Current

|                 |      |
|-----------------|------|
| Amperage Rating | 60 A |
|-----------------|------|

## Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/2" |
|----------|--------|

## General

|                 |                                              |
|-----------------|----------------------------------------------|
| Receptacle Type | Mechanically Interlocked                     |
| Type            | Pin & Sleeve                                 |
| Series          | VBQ Series                                   |
| Material        | Aluminum, Copper Free (less than 4/10 of 1%) |
| UPC             | 783936835389                                 |

## Product Assets

[Catalog \[English\]](#)