



VE3Q0036E30 - VE3 36W Emergency Only, 120-277 CFL Quad-Pin Class I Div. 2

By Killark
Catalog # [VE3Q0036E30](#)

VE3 36W Emergency Only, 120-277 CFL Quad-Pin Class I Div. 2



Features

- Quad-Pin triple-tube long-life compact fluorescent lamps included
- World Voltage 120-277VAC 50-60 Hz
- LED charging indicator light visible through lens
- Prewired terminal block for easy power connection
- Two lamp models include two independent redundant systems
- Six mounting splice box types - Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion.
- Normally shipped as components for fast delivery or may be ordered factory assembled.
- Options for Fuses and Quick Disconnect

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Division 2, Groups F, G • Class III, Divisions 1 & 2
IP Rating	IP66
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Lumens Per Watt	22.2
Wattage	36 W
Voltage Rating	120-277 VAC

General

Series	VE3Q Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Optic Type	Luminaire Only
UPC	783936079431
Light Source	Compact Fluorescent
Mounting Type	Luminaire Only

Operational

Lumens	800
Lumen Range	0-2,000 lm

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)