



VFBGG2-100PXGSU117 - 100W V Series Incandescent 3/4" Wall Mount to VBC Splice Box with Guard - Unit Pack - Green Globe

By Killark
Catalog # [VFBGG2-100PXGSU117](#)

100W V Series Incandescent 3/4" Wall Mount to VBC Splice Box with Guard - Unit Pack - Green Globe

Features

- Electrostatically applied epoxy/polyester finish
- Modular design
- Hubs are threaded for attachment to conduit
- Set screws in pendant fixture
- Copper-free aluminum (less than .004%)

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Wattage	150 W
Voltage Rating	120-277 VAC



Dimensions

Hub Size	3/4"
----------	------

General

Series	V Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Lamp Type	Medium Base
Optic Type	Glass Globe - Clear
UPC	783936059839
Light Source	Incandescent
Mounting Type	Ceiling

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)