



VM3H076NR - VM3 Series - 70W Metal Halide 120/277/347V with Ex nR

By Killark
Catalog # [VM3H076NR](#)

VM3 Series - 70W Metal Halide 120/277/347V with Ex nR



Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4” glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types.
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors.
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect.

Specifications

EU RoHS Indicator	Contact Manufacturer
Current	
Frequency Rating	60 Hz
Voltage Rating	Tri - 120/277/347 VAC
Wattage	70 W
General	
Optic Type	Luminaire Only
Mounting Type	Luminaire Only
UPC	783936009070
Light Source	Metal Halide
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Series	VM3 Series