



VM3H100NR - VM3 Series - 100W Metal Halide Quadri-Volt with Ex nR

By Killark
Catalog # VM3H100NR

VM3 Series - 100W Metal Halide Quadri-Volt with Ex nR



Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4” glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types.
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors.
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect.

Specifications

EU RoHS Indicator		Contact Manufacturer
Current		
Frequency Rating	60 Hz	
Voltage Rating	Quad - 120/277/347/480 VAC	
Wattage	100 W	
General		
Optic Type	Luminaire Only	
Mounting Type	Luminaire Only	
UPC	783936009087	
Light Source	Metal Halide	
Material	Aluminum, Copper Free (less than 4/10 of 1%)	
Finish Type	Powder Epoxy Paint	
Series	VM3 Series	