



VM5S406 - VM5 Series, AL 400 W High Wattage High Pressure Sodium Light Fixture (Lamp Not Included), Optic Thread Size 7-3/4", 120/277/347V, 60Hz

By Killark
Catalog # VM5S406

VM5 Series - Aluminum 400 Watt High Wattage High Pressure Sodium Light Fixture (Lamp Not Included) - Optic Thread Size 7-3/4 Inch - 120/277/347V At 60Hz

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4" glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect

Specifications

- Hazardous Rating(s)
- Class I, Division 2, Groups A, B, C, D
 - Class I, Zone 2, Groups IIC, IIB, IIA



EU RoHS Indicator

Current

- Frequency Rating
- 60 Hz
- Voltage Rating
- Tri - 120/277/347 VAC
- Wattage
- 400 W

General

- Optic Type
- Luminaire Only
- Lamp Type
- Mogul Base
- Mounting Type
- Luminaire Only
- UPC
- 783936966885
- Light Source
- High Pressure Sodium
- Material
- Aluminum, Copper Free (less than 4/10 of 1%)
- Finish Type
- Powder Epoxy Paint
- Series
- VM5 Series

Logistics

- Carton Quantity
- 1

- Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer