



VM5S606 - VM5 Series, AL 600 W High Wattage High Pressure Sodium Light Fixture (Lamp Not Included), Optic Thread Size 7-3/4", 120/277/347V, 60Hz

By Killark
Catalog # VM5S606

VM5 Series - Aluminum 600 Watt High Wattage High Pressure Sodium Light Fixture (Lamp Not Included) - Optic Thread Size 7-3/4 Inch - 120/277/347V At 60Hz

Features

- Ballast tank and splice box – corrosion resistant copper-free aluminum alloy with baked powder epoxy/polyester finish, electrostatically applied for complete, uniform corrosion protection.
- All external hardware – 316 stainless steel.
- Guards – painted copper-free aluminum alloy or 316SS for 7-3/4" glass optics and Enclosed Reflectors.
- Spin-top Refractor Guards are Plated Steel.
- Reflectors – lightweight, corrosion resistant fiberglass reinforced polyester, or copper-free aluminum.
- Seven mounting splice box types
- Pendant, Flex Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion – in a variety of entry sizes, including M20 for the VMX ceiling style.
- Quartz auxiliary, HPS instant restart, Ballast Protectors
- Normally shipped as components for fast delivery, or may be ordered factory assembled with or without lamps.
- Options for fuses and quick disconnect

Specifications

- Hazardous Rating(s)
- Class I, Division 2, Groups A, B, C, D
 - Class I, Zone 2, Groups IIC, IIB, IIA



EU RoHS Indicator

Current

Frequency Rating
Voltage Rating
Wattage

- Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer

60 Hz
Tri - 120/277/347 VAC
600 W

General

Optic Type
Lamp Type
Mounting Type
UPC
Light Source
Material

Finish Type
Series

Luminaire Only
Mogul Base
Luminaire Only
783936966915
High Pressure Sodium
Aluminum, Copper Free (less than 4/10 of 1%)
Powder Epoxy Paint
VM5 Series

Logistics

Carton Quantity 1