



# VML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen 1" Wall Bracket

By Killark  
Catalog # [VML1X730B3G](#)



VML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen  
1" Wall Bracket

## Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

## Application

Class I Division 2 Hazardous Locations;Class II Hazardous Dust;Zone 2 Hazardous Locations;Off and On Shore Oil and Gas;Wet and Marine Locations;Food and Beverage;Heavy Industrial

## Specifications

|                     |                                                                                                                                                                                                                                                                                                |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEx QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS 22ATEX7000</li></ul> |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Current

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 0.46-0.20 A |
| Frequency Rating          | 50-60 Hz    |
| Wattage                   | 55 W        |
| Voltage Rating            | 120-277 VAC |

## Dimensions

|          |    |
|----------|----|
| Hub Size | 1" |
|----------|----|

## General

|               |                    |
|---------------|--------------------|
| Optic Type    | Glass Globe        |
| Series        | VML-X Series       |
| Light Source  | LED                |
| Mounting Type | Wall Bracket       |
| Finish Type   | Powder Epoxy Paint |

## Operational

|                   |                  |
|-------------------|------------------|
| Color Temperature | 5000 K           |
| Lumens            | 7000             |
| Lumen Range       | 5,000 - 9,000 lm |

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)