



# VML-X Series LED Area light 75 Watt, 120-277VAC, 9000 Lumen 1-1/4" Straight Stanchion

By Killark  
Catalog # [VML1X930S4G](#)

VML-X Series LED Area light 75 Watt, 120-277VAC, 9000 Lumen 1-1/4" Straight Stanchion



## Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

## Application

Class I Division 2 Hazardous Locations;Class II Hazardous Dust;Zone 2 Hazardous Locations;Off and On Shore Oil and Gas;Wet and Marine Locations;Food and Beverage;Heavy Industrial

## Specifications

|                     |                                                                                                                                                                                                                                                                                                |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEX QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS 22ATEX7000</li></ul> |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

## Current

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 0.63-0.27 A |
| Frequency Rating          | 50-60 Hz    |
| Wattage                   | 75 W        |
| Voltage Rating            | 120-277 VAC |

## Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

## General

|               |                    |
|---------------|--------------------|
| Optic Type    | Glass Globe        |
| Series        | VML-X Series       |
| Light Source  | LED                |
| Mounting Type | Straight Stanchion |
| Finish Type   | Powder Epoxy Paint |

## Operational

|                   |                  |
|-------------------|------------------|
| Color Temperature | 5000 K           |
| Lumens            | 9000             |
| Lumen Range       | 5,000 - 9,000 lm |

## Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)