



## VML-X Series LED Area light 100 Watt, 120-277VAC, 12000 Lumen 1-1/4" 25° Stanchion Mount

By Killark

Catalog # [VML2X1230D4G](#)

VML-X Series LED Area light 100 Watt, 120-277VAC, 12000 Lumen 1-1/4" 25° Stanchion Mount

### Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

### Application

Class I Division 2 Hazardous Locations; Class II Hazardous Dust; Zone 2 Hazardous Locations; Off and On Shore Oil and Gas; Wet and Marine Locations; Food and Beverage; Heavy Industrial

### Specifications

|                     |                                                                                                                                                                                                                                                                                                |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hazardous Rating(s) | <ul style="list-style-type: none"><li>• Class I, Div2, Groups A,B,C,D</li><li>• Class I, Zone 2, Groups IIC, IIB, IIA</li><li>• Class II, Div. 1&amp;2, Groups E,F,G</li><li>• IECEX QPS 15.0006</li><li>• Ex ec IIC T4/T3 Gc</li><li>• Ex tb IIIC T4/T3 Db</li><li>• QPS 22ATEX7000</li></ul> |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|



### Current

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 0.83-0.36 A |
| Frequency Rating          | 50-60 Hz    |
| Wattage                   | 100 W       |
| Voltage Rating            | 120-277 VAC |

### Dimensions

|          |        |
|----------|--------|
| Hub Size | 1-1/4" |
|----------|--------|

### General

|               |                    |
|---------------|--------------------|
| Optic Type    | Glass Globe        |
| Series        | VML-X Series       |
| Light Source  | LED                |
| Mounting Type | 25° Stanchion      |
| Finish Type   | Powder Epoxy Paint |

### Operational

|                   |                    |
|-------------------|--------------------|
| Color Temperature | 5000 K             |
| Lumens            | 12000              |
| Lumen Range       | 12,000 - 18,000 lm |

### Product Assets

[Catalog \[English\]](#)  
[Catalog Page \[English\]](#)  
[Installation Manual \[French, English\]](#)



A Hubbell brand