



VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 3/4" Cone Mount

By Killark

Catalog # [VML3X2830C2G](#)

VML-X Series LED Area light 250 Watt, 120-277VAC, 28000 Lumen 3/4" Cone Mount



Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Application

Class I Division 2 Hazardous Locations; Class II Hazardous Dust; Zone 2 Hazardous Locations; Off and On Shore Oil and Gas; Wet and Marine Locations; Food and Beverage; Heavy Industrial

Specifications

Hazardous Rating(s)	• Class I, Div2, Groups A,B,C,D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Div. 1&2, Groups E,F,G • IECEX QPS 15.0006 • Ex ec IIC T4/T3 Gc • Ex tb IIIC T4/T3 Db • QPS 22ATEX7000
---------------------	--

Current

Current / Amperage Rating	2.08-0.09 A
Frequency Rating	50-60 Hz
Wattage	250 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	3/4"
----------	------

General

Optic Type	Glass Globe
Series	VML-X Series
Light Source	LED
Mounting Type	Cone
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	28000
Lumen Range	23,000 - 28,000 lm

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

[Installation Manual \[French, English\]](#)



A Hubbell brand