



VOBG-100 SU104 - 100W V Series
Incandescent Ceiling Mount With VBA
Adapter For Round Outlet Box with Guard
- Unit Pack

By Killark
Catalog # [VOBG-100 SU104](#)

100W V Series Incandescent Ceiling Mount With VBA Adapter
For Round Outlet Box with Guard - Unit Pack

Features

- Electrostatically applied epoxy/polyester finish
- Modular design
- Hubs are threaded for attachment to conduit
- Set screws in pendant fixture
- Copper-free aluminum (less than .004%)

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Wattage	150 W
Voltage Rating	120-277 VAC



Dimensions

Hub Size	1/2"
----------	------

General

Series	V Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Lamp Type	Medium Base
Optic Type	Glass Globe - Clear
UPC	783936062686
Light Source	Incandescent
Mounting Type	Ceiling

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)