



# Versamate Series 60A 4P 4W Polarized Connector Assembly

By Killark  
Catalog # [VPR6455-S37](#)

60A 4W4P Polarized Connector Assembly

## Features

- Feature an octagonal body style, ensuring a sure grip when connecting or disconnecting.
- Insulators have high mechanical and dielectric strength.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Funneled conductor entry chambers lead all properly stripped conductors into terminals simultaneously.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Includes suitability for Type P marine cable.

## Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

## Specifications

|                          |                      |
|--------------------------|----------------------|
| EU RoHS Indicator        | Contact Manufacturer |
| Buy America(n) Qualified | Contact Manufacturer |

## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 4 |
|-----------------|---|

## Current

|                  |           |
|------------------|-----------|
| Amperage Rating  | 60 A      |
| Frequency Rating | 50-400 Hz |



|                |                                                                             |
|----------------|-----------------------------------------------------------------------------|
| Voltage Rating | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |
|----------------|-----------------------------------------------------------------------------|

## Dimensions

|               |                             |
|---------------|-----------------------------|
| Width         | 4.37 in                     |
| Height        | 4.37 in                     |
| Grommet Range | 0.65-1.50                   |
| Length        | 9.68 in                     |
| Dimensions    | 9.68 in x 4.37 in x 4.37 in |

## General

|             |                                                                                                                                                                                                         |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type        | Pin & Sleeve                                                                                                                                                                                            |
| Series      | VersaMate Series                                                                                                                                                                                        |
| Material    | <ul style="list-style-type: none"><li>• Body-Copper-free aluminum</li><li>• Contacts-Brass</li><li>• Spring tensioner-Patented beryllium copper</li><li>• External screws-316 stainless steel</li></ul> |
| Finish Type | Baked Powder Epoxy/Polyester Finish                                                                                                                                                                     |
| UPC         | 783936398853                                                                                                                                                                                            |
| Style       | Style I                                                                                                                                                                                                 |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)