



VQ2F6419 - VQ2F Series - Aluminum 64 Watt Compact Fluorescent Light Fixture (Two 32W Lamps Included) - 120VDC - Optic Thread Size 7-3/4Inch

By Killark
Catalog # [VQ2F6419](#)

VQ2F Series - Aluminum 64 Watt Compact Fluorescent Light Fixture (Two 32W Lamps Included) - 120VDC - Optic Thread Size 7-3/4Inch

Features

- World Voltage Ballast 120 through 277 VAC 50/60Hz
- Six mounting splice box types: Pendant, Ceiling, Wall bracket, Cone Top, 25° Angle Stanchion, Straight Stanchion - in a variety of entry sizes, including M20 for the VMX ceiling style.
- Elevated ambients to 55°C 13W - 64W
- Two lamp models have 2 ballasts for separate switching or system redundancy
- Normally shipped as components for fast delivery, or may be ordered factory assembled.
- Options for Fuses and Quick Disconnect
- Tank assemblies include quad-pin lamp

Specifications

Hazardous Rating(s)	• Class I, Division 2, Groups A, B, C, D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current



Lumens Per Watt	75
Wattage	64 W
Voltage Rating	120 VDC
General	
Series	VQ2F Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Finish Type	Powder Epoxy Paint
Lamp Type	Quad Pin
Optic Type	Luminaire Only
UPC	783936095387
Light Source	Compact Fluorescent
Mounting Type	Luminaire Only

Logistics

Carton Quantity	1
-----------------	---

Operational

Lumens	4800
Lumen Range	2,001-5,000 lm

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)