



Versamate Series 100A 3 Pole 3 Wire Receptacle with E Type Box 1-1/4" - Reverse Service

By Killark
Catalog # [VR1031E4-S39](#)

100A 3 Pole 3 Wire Receptacle with E Type Box 1-1/4" - Reverse Service

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	3
-----------------	---

Configuration

Back Box Type	DEAD END
---------------	----------

Current

Amperage Rating	100 A
Frequency Rating	50-400 Hz
Voltage Rating	• 600 VAC • 250 VDC

Dimensions

Hub Size	1-1/4"
Width	6.11 in
Height	8 in
Length	8.62 in
Dimensions	8.62 in x 6.11 in x 8 in

General

Type	Pin & Sleeve
Series	VersaMate Series
Material	• Body-Copper-free aluminum • Contacts-Brass • Spring tensioner-Patented beryllium copper • External screws-316 stainless steel
Finish Type	Baked Powder Epoxy/Polyester
UPC	783936063096
Style	Style I

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)