



Versamate Series 100A 3 Pole 4 Wire Receptacle Assembly - AT Type

By Killark

Catalog # [VR1034](#)

100A 3 Pole 4 Wire Receptacle Assembly - AT Type



Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

Application

Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

Specifications

EU RoHS Indicator

Contact Manufacturer

Buy America(n) Qualified

Contact Manufacturer

Conductor

Number Of Wires

3

Current

Amperage Rating

100 A

Frequency Rating

50-400 Hz

Voltage Rating

- 600 VAC

- 250 VDC

Dimensions

Width

4.25 in

Weight

3.48 lb.

Height

4.75 in

Length

5.37 in

Dimensions

5.37 in x 4.25 in x 4.75 in

General

Type

Pin & Sleeve

Series

VersaMate Series

Material

- Body-Copper-free aluminum
- Contacts-Brass
- Spring tensioner-Patented beryllium copper
- External screws-316 stainless steel

Finish Type

Baked Powder Epoxy/Polyester Finish

UPC

783936078656

Style

Style I

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved

KILL-VR1034-SPEC-EN | REV 1/2026