



# Versamate Series 30A 2 Pole 3 Wire Receptacle Assembly - Reverse Service

By Killark  
Catalog # [VR332-S39](#)

30A 2 Pole 3 Wire Receptacle Assembly - Reverse Service

## Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.
- Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

## Application


Suitable for indoor or outdoor use. Applications include the wet, cold, hosedown, hazardous or corrosive areas in such industrial applications as:Pulp & Paper Mills, Electrical Power Plants, Petrochemical Plants, Wastewater Treatment, Marine, Docks, Ports, Construction Sites, Breweries, Refineries, Chemical Plants, Grain Facilities , Textile Manufacturing, Food Processing Facilities

## Specifications

|                          |                      |
|--------------------------|----------------------|
| EU RoHS Indicator        | Contact Manufacturer |
| Buy America(n) Qualified | Contact Manufacturer |

## Conductor

|                 |   |
|-----------------|---|
| Number Of Wires | 2 |
|-----------------|---|



## Current

|                  |                                                                             |
|------------------|-----------------------------------------------------------------------------|
| Amperage Rating  | 30 A                                                                        |
| Frequency Rating | 50-400 Hz                                                                   |
| Voltage Rating   | <ul style="list-style-type: none"><li>• 600 VAC</li><li>• 250 VDC</li></ul> |

## Dimensions

|            |                             |
|------------|-----------------------------|
| Width      | 3.41 in                     |
| Height     | 3.89 in                     |
| Length     | 3.25 in                     |
| Dimensions | 3.25 in x 3.41 in x 3.89 in |

## General

|             |                                                                                                                                                                                                         |
|-------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Type        | Pin & Sleeve                                                                                                                                                                                            |
| Series      | VersaMate Series                                                                                                                                                                                        |
| Material    | <ul style="list-style-type: none"><li>• Body-Copper-free aluminum</li><li>• Contacts-Brass</li><li>• Spring tensioner-Patented beryllium copper</li><li>• External screws-316 stainless steel</li></ul> |
| Finish Type | Baked Powder Epoxy/Polyester Finish                                                                                                                                                                     |
| UPC         | 783936376134                                                                                                                                                                                            |
| Style       | Style II                                                                                                                                                                                                |

## Product Assets

[Catalog \[English\]](#)