



Versamate Series 30A 2 Pole 3 Wire Receptacle - D Type Box - 1/2"

By Killark
Catalog # [VR332D1](#)

VERSA RECPT STYLE II 30A 2W3P DTYPE 1/2"

Features

- Patented “Breech-Lock” cap serves as both flip lid and screw cover.
- Patented notch in cap arm holds cap open for easy plug insertion or maintenance.
- Type 4X rating when inserted into VersaMate receptacle and locking ring is tightened.Patented pin design uses slotted spring clip which avoids excessive wear while providing continuous electrical pin to sleeve contact.
- “Increased Safety” type box terminals with gripper ribs securely clamp around conductors.
- Boxes come with a green grounding screw.

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	3
Number Of Poles	2

Configuration

Back Box Type	ANGLED FEED THRU
---------------	------------------

Current



Amperage Rating	30 A
Frequency Rating	50-400 Hz
Voltage Rating	• 653 VAC • 250 VDC

Dimensions

Hub Size	1/2"
----------	------

General

Type	Pin & Sleeve
Series	VersaMate Series
Material	• Body-Copper-free aluminum • Contacts-Brass • Spring tensioner-Patented beryllium copper • External screws-316 stainless steel
Finish Type	Baked Powder Epoxy/Polyester Finish
UPC	783936842332
Style	Style II

Product Assets

[Catalog \[English\]](#)