



VSQ Series 60A 2P 3W Factory Sealed Hazardous Interlocked Receptacle - Cover Only

By Killark
Catalog # [VSQ6023FS-COV](#)

60A 2W3P VSQ Factory Sealed Hazardous Interlocked Receptacle - Cover Only

Features

- Factory Sealed Construction
- Compact size and footprint
- Plug Interlock Mechanism for Dead-Front construction. Switch cannot be turned “ON” without fully inserted plug. Plug cannot be removed with switch in “ON” position
- Factory Wired Receptacle (Load Side)
- “Off” position is padlockable for maintenance safety
- Auxiliary Contact (late-make early-break) rated 10 Amp, 1/3 HP at 125/250 VAC.
- Adjustable mounting lugs
- Feed-through construction
- Horsepower-rated internal switch

Specifications

Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups B, C, D • Class I, Zones 1 & 2, Groups IIB+H2, IIA • Class II, Divisions 1 & 2, Groups F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3, 4, 4X, 7(B, C, D), 9(F, G)



Buy America(n) Qualified	Contact Manufacturer
Conductor	
Number Of Wires	3
Number Of Poles	2
Current	
Amperage Rating	60 A
General	
Receptacle Type	Mechanically Interlocked
Type	Pin & Sleeve
Series	VSQ-FS
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936012476
Logistics	
Factory Sealed	Factory Sealed
Product Assets	
Catalog [English]	
Installation Manual [English]	