



VUHG-2-100 - 100W V Series Incandescent
- Ceiling Mount with VGH Splice Box -
Dead End - 3/4" Hub

By Killark
Catalog # [VUHG-2-100](#)

100W V Series Incandescent - Ceiling Mount with VGH Splice Box
- Dead End - 3/4" Hub

Features

- Electrostatically applied epoxy/polyester finish
- Modular design
- Hubs are threaded for attachment to conduit
- Set screws in pendant fixture
- Copper-free aluminum (less than .004%)

Specifications

EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer

Current

Frequency Rating	50/60 Hz
Wattage	150 W
Voltage Rating	120-277 VAC

Dimensions

Hub Size	3/4"
----------	------

General

Series	V Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Lamp Type	Medium Base
Optic Type	Glass Globe - Clear
UPC	783936824406
Light Source	Incandescent
Mounting Type	Ceiling

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)

