



COMPACT SIZE – COMPONENTS



MB MOUNTING BRACKETS				
CATALOG NUMBER				HUB SIZE
PENDANT	CEILING	WALL	STANCHION	
MBA-2	MBX-2	MBB-2	—	3/4"
MBA-3	MBX-3	MBB-3	—	1"
—	MBX-8*	—	—	M20
—	—	—	MBD-4	1-1/4"
—	—	—	MBD-5	1-1/2"

\* MBX-8 furnished with 3 non-metallic plugs



**Non-Glass Polycarbonate  
8" Flat Lens or Spin-top**



MBL LED OPTICS AND ACCESSORIES		
DESCRIPTION	OPTIC LOGIC	GUARD
Globe (glass)	MBG (GL)	MBAG
Reflector (all glass) Type V	VMR175 (R5)	VMAG17
Reflector (spin top) 8" Type V	VZRG1550 (S8)	VMRWG8
Reflector (spin top) 12" Type V	VZRG2550 (S5)	VMRWGS
8" Spin-top flat lens (glass)Ⓞ	VZRGF8 (GF)	VZRF8GRD
8" Spin-top flat lens (polycarbonate)Ⓞ	VZRPF8 (PF)	VZRF8GRD
Reflector polycarbonate (spin -top) 12" Type V	VZRP175 (P5)	VMRWGS
Pathway ReflectorⓄ	VZRF8PR	NA
Reflector for MBG Globe - DOMEⓄ	VMPSD-17	NA
Reflector for MBG Globe - ANGLEⓄ	VMPA-17	NA
120VAC Photocell with FS Style Cover	VMFSPC1	NA
208-277VAC Photocell with FS Style Cover	VMFSPC2	NA
3-sided EXIT Accessory (use without guard)	VEXA100B	NA

Ⓞ 14-25W only

Ⓞ Reflectors for use with MBG/MBAG only; VMG17 globe with VMAG17 guard will fit without reflector.



## COMPONENTS



Pendant



Ceiling



Wall



Cone Top



25° Stanchion



Straight Stanchion



EZ Adapter\*  
VMEZA



Tank Adapter

### MOUNTING SPLICE BOXES

#### CATALOG NUMBER

HUB SIZE	PENDANT	FLEXIBLE PENDANT	CEILING 4 HUB	CEILING 5 HUB	WALL	CONE TOP	25 DEGREE STANCHION	90 DEGREE STANCHION
3/4"	VMA2B	VMF2B	VMX2B	VMX6B	VMB2B	VMC2B	—	—
1"	VMA3B	VMF3B	VMX3B	VMX7B	VMB3B	VMC3B	—	—
1-1/4"	—	—	—	—	—	—	VMD4B	VMS4B
1-1/2"	—	—	—	—	—	—	VMD5B	VMS5B
M-20	—	—	VMX8B**	VMX9B	—	—	—	—

\*VMEZA is used between a ballast tank and an EZ mount-ordered separately. See L83 for more information.

\*\*VMX8B furnished with 3 non-metallic plugs.

### OPTICS & GUARDS

DESCRIPTION	5-1/2" Optic Thread Size		7-3/4" Optic Thread Size	
	OPTICS	GUARD	OPTICS	GUARD
Globe (glass)	VMG17	VMAG17	VMG25	VMAG25S
Refractor (all glass) Type V	VMR175	VMAG17	VMR255	VMAG25S
Refractor (all glass) Type I	VMR171	VMAG17	VMR251	VMAG25S
Refractor (all glass) Type III	—	—	VMR253	VMAG25S
Refractor (spin top glass) 8" Type V	VZRG1550	VMRWG8	—	—
Refractor (spin top glass) 12" Type V	VZRG2550	VMRWG	VZRG4050	VMRWG
Refractor (spin top glass) 12" Type II	VZRG2520	VMRWG	VZRG4020	VMRWG
Refractor (spin top plastic) 12" Type V	VZRP175	VMRWG	—	—
Enclosed Reflector (glass lens)	—	—	VMER40	VMERG
Enclosed Reflector (plastic lens)	—	—	VMEP40	—



DE3B/VE3B/VE3Q  
5-1/2" Optic



DE4B/VE4B/VE4Q  
7-3/4" Optic

OPTICS	OPTICS									
	VMG17	VMR175 VMR171	VZRG1550	VZRG2550 VZRG2520 VZRP175	VMG25	VMR255 VMR253 VMR251	VMG40	VMER40	VZRG4050 VZRG4020	VMEP40
GUARDS	GUARDS									
	VMAG17	VMAG17	VMRWG8	VMRWGS	VMAG25S	VMAG25S	VMAG40S	VMERG	VMRWG8	VMRWG8

### REFLECTORS

<b>VMPSD40</b>	<b>VMPA40</b>	<b>HRD400</b>	<b>HRD400ALZ</b>	<b>VMAGBC</b>
Standard Dome Fiberglass White Reflector Dia: 16"	30 O Angle Fiberglass White Reflector Dia: 16"	Deep Aluminum White Reflector Dia: 21"	Deep Aluminum Anodized Reflector Dia: 21"	Bottom Closure for VMAG25S/VMAG40S