



VM2&4LB, VM2&4LC SERIES

HIGH WATTAGE – COMPONENTS



Pendant



Ceiling



Wall



Cone Top



25° Stanchion



Straight Stanchion



EZ Adapter*
VMEZA



Tank Adapter
See next page to order

CERTILITE® VM MOUNTING SPLICE BOXES

HUB SIZE	CATALOG NUMBER						
	PENDANT	CEILING 4 HUB	CEILING 5 HUB	WALL	CONE TOP	25 DEGREE STANCHION	90 DEGREE STANCHION
3/4"	VMA2B	VMX2B	VMX6B	VMB2B	VMC2B	—	—
1"	VMA3B	VMX3B	VMX7B	VMB3B	VMC3B	—	—
1-1/4"	—	—	—	—	—	VMD4B	VMS4B
1-1/2"	—	—	—	—	—	VMD5B	VMS5B
M-20	—	VMX8B**	VMX9B**	VMB8B**	—	—	—

* VMEZA is used between a ballast tank and an EZ mount - ordered separately. See catalog grids.

** Furnished with Ⓢ non-metallic plugs. Also available: VMB10B wall 4xM25 hubs, and VMB810B 2xM20 side hubs and 2xM25 top/bottom

VM2L/VM4L LED OPTICS AND ACCESSORIES

DESCRIPTION	OPTIC LOGIC	GUARDⓈ
Flat Lens (glass spin top) "C" tank only	VZRGF12 (GF)	VZRF12GRD
Flat Lens (polycarbonate spin top) "C" tank only*	VZRP12 (PF)	VZRF12GRD
Globe (glass)	VMG25 (GL)	VMAG25S
Refractor (all glass) Type V	VMR255 (R5)	VMAG25S
Enclosed Reflector	VMER40 (ER)	VMERG
Enclosed Reflector with polycarbonate Lens*	VMEP40 (EP)Ⓢ	—
Refractor (polycarbonate spin top) 12" Type V*	VZRP175B (P5)	VMRWGS
Refractor (glass spin top) 12" Type V	VZRG4050 (S5)	VMRWGS

* Non-glass over Food/Grain Class II Div 1 Group G Certified; VMEP40, VZRP175B, and VZRP12

VM2L/VM4L LED REFLECTORS AND ACCESSORIES

DOME REFLECTOR (Polyester reinforced fiberglass)	VMPSD40
ANGLE REFLECTOR (Polyester reinforced fiberglass)	VMPA40
DEEP DOME REFLECTOR (White Painted Aluminum)	HRD400
DEEP DOME REFLECTOR (Anodized Aluminum)	HRD400ALZ
120VAC Photocell with FS Style CoverⓈ	VMFSPC1
208-277VAC Photocell with FS Style CoverⓈ	VMFSPC2
Bottom Closure for VMAG25SⓈ	VMAGBC
4-sided EXIT Accessory (use without guard)Ⓢ	VEXA400

Ⓢ Order single-gang FS box separately. For photocell factory installed in tank, see logic.

Ⓢ For use with Generator or UPS powered fixtures

Ⓢ For wall applications mount must be spaced out for bottom hub

Ⓢ Guards are 316 Stainless Steel. Bottom closure for VMAG25S pt. no. VMAGBC



VMG25



VMR255
VMR253
VMR251



VMAG25S



VMAGBC



VMER40



VMERG



VMEP40



VZRG4050
VZRG4020



VMRWGS



VZRPF/VZRGF



VMPSD40

Standard Dome, Fiberglass
White Reflector, Dia: 16"



VMPA40

300 Angle, Fiberglass
White Reflector, Dia:16"



VMFSPC



VEXA400
Fixture not included



HRD400

Deep Aluminum, White
Reflector, Dia: 21"



HRD400ALZ

Deep Aluminum, Anodized
Reflector, Dia: 21"