



WML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen 3/4" Wall Bracket

By Killark
Catalog # [WML1X730B2G](#)



WML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen 3/4" Wall Bracket

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Specifications

Environmental Conditions	• Suitablefor Wet Locations • Type 3, 4X • IP66 • Marine Rated (US Only)
--------------------------	--

Current

Current / Amperage Rating	0.46-0.20 A
Frequency Rating	50-60 Hz
Wattage	55 W

Voltage Rating	120-277 VAC
----------------	-------------

Dimensions

Hub Size	3/4"
----------	------

General

Optic Type	Glass Globe
Series	WML-X Series
Light Source	LED
Mounting Type	Wall Bracket
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	7000
Lumen Range	5,000 - 9,000 lm

Product Assets

[Catalog Page \[English\]](#)