



WML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen Driver Tank

By Killark
Catalog # [WML1X730G](#)



WML-X Series LED Area light 55 Watt, 120-277VAC, 7000 Lumen Driver Tank

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Specifications

Hazardous Rating(s)	• Class I, Div2, Groups A,B,C,D • Class I, Zone 2, Groups IIC, IIB, IIA • Class II, Div. 1&2, Groups E,F,G • IECEX QPS 15.0006 • Ex ec IIC T4/T3 Gc • Ex tb IIIC T4/T3 Db • QPS22ATEX7000
Environmental Conditions	• Suitablefor Wet Locations • Type 3, 4X • IP66 • Marine Rated (US Only)

Current

Current / Amperage Rating	0.46-0.20 A
Frequency Rating	50/60 Hz
Wattage	55 W
Voltage Rating	120-277 VAC

General

Series	WML-X Series
Finish Type	Powder Epoxy Paint
Optic Type	Glass Globe
UPC	783936186924
Light Source	LED

Operational

Color Temperature	5000 K
Lumens	7000
Lumen Range	5,000 - 9,000 lm

Product Assets

[Catalog Page \[English\]](#)