



# WML-X Series LED Area light 100 Watt, 120-277VAC, 12000 Lumen 1" Wall Bracket

By Killark  
Catalog # [WML2X1230B3G](#)

WML-X Series LED Area light 100 Watt, 120-277VAC, 12000  
Lumen 1" Wall Bracket



## Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

## Specifications

|                          |                                                                                                                                                  |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Environmental Conditions | <ul style="list-style-type: none"><li>• Suitablefor Wet Locations</li><li>• Type 3, 4X</li><li>• IP66</li><li>• Marine Rated (US Only)</li></ul> |
|--------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|

## Current

|                           |             |
|---------------------------|-------------|
| Current / Amperage Rating | 0.83-0.36 A |
| Frequency Rating          | 50-60 Hz    |
| Wattage                   | 100 W       |

|                |             |
|----------------|-------------|
| Voltage Rating | 120-277 VAC |
|----------------|-------------|

## Dimensions

|          |    |
|----------|----|
| Hub Size | 1" |
|----------|----|

## General

|               |                    |
|---------------|--------------------|
| Optic Type    | Glass Globe        |
| Series        | WML-X Series       |
| Light Source  | LED                |
| Mounting Type | Wall Bracket       |
| Finish Type   | Powder Epoxy Paint |

## Operational

|                   |                    |
|-------------------|--------------------|
| Color Temperature | 5000 K             |
| Lumens            | 12000              |
| Lumen Range       | 12,000 - 18,000 lm |

## Product Assets

[Catalog Page \[English\]](#)