



WML-X Series LED Area light 100 Watt, 120-277VAC, 12000 Lumen 1" Cone Mount

By Killark
Catalog # [WML2X1230C3G](#)



WML-X Series LED Area light 100 Watt, 120-277VAC, 12000 Lumen 1" Cone Mount

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Specifications

Environmental Conditions	• Suitablefor Wet Locations • Type 3, 4X • IP66 • Marine Rated (US Only)
--------------------------	--

Current

Current / Amperage Rating	0.83-0.36 A
Frequency Rating	50-60 Hz
Wattage	100 W

Voltage Rating	120-277 VAC
----------------	-------------

Dimensions

Hub Size	1"
----------	----

General

Optic Type	Glass Globe
Series	WML-X Series
Light Source	LED
Mounting Type	Cone
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	12000
Lumen Range	12,000 - 18,000 lm

Product Assets

[Catalog Page \[English\]](#)