



WML-X Series LED Area light 140 Watt,
120-277VAC, 18000 Lumen 3/4" Pendant
Mount

By Killark
Catalog # [WML2X1830A2G](#)

WML-X Series LED Area light 140 Watt, 120-277VAC, 18000
Lumen 3/4" Pendant Mount

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Finless Design
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Specifications

Environmental Conditions	• Suitablefor Wet Locations • Type 3, 4X • IP66 • Marine Rated (US Only)
--------------------------	--

Current

Current / Amperage Rating	1.17-0.51 A
Frequency Rating	50-60 Hz
Wattage	140 W



Voltage Rating	120-277 VAC
----------------	-------------

Dimensions

Hub Size	3/4"
----------	------

General

Optic Type	Glass Globe
Series	WML-X Series
Light Source	LED
Mounting Type	Pendant
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	18000
Lumen Range	12,000 - 18,000 lm

Product Assets

[Catalog Page \[English\]](#)