



WML-X Series LED Area light 200 Watt, 120-277VAC, 23000 Lumen 3/4" Pendant Mount

By Killark
Catalog # [WML3X2330A2G](#)

WML-X Series LED Area light 200 Watt, 120-277VAC, 23000 Lumen 3/4" Pendant Mount

Features

- Energy Efficient and Long Life LED's
- Walkway Optic patterns
- Easy Retrofit to Competitors
- Lighter Weight
- LED Color of 5000K with 80 CRI
- Wildlife Friendly Color options

Specifications

Environmental Conditions	• Suitablefor Wet Locations • Type 3, 4X • IP66 • Marine Rated (US Only)
--------------------------	--

Current

Current / Amperage Rating	1.67-0.72 A
Frequency Rating	50-60 Hz
Wattage	200 W
Voltage Rating	120-277 VAC



Dimensions

Hub Size	3/4"
----------	------

General

Optic Type	Glass Globe
Series	WML-X Series
Light Source	LED
Mounting Type	Pendant
Finish Type	Powder Epoxy Paint

Operational

Color Temperature	5000 K
Lumens	23000
Lumen Range	23,000 - 28,000 lm

Product Assets

[Catalog Page \[English\]](#)