



XEDS-30 SU-40 - XEDS Series, 30 Amp Disconnect Switch with Lock "On"

By Killark
Catalog # [XEDS-30 SU-40](#)

XEDS Series, 30 Amp Disconnect Switch with Lock "On"



Features

- External handle is vault type with standard provisions for locking in "OFF" position with up to three padlocks.
- Provisions for locking in "ON" position available as factory modification (add suffix SU40 to catalog number).
- Enclosure and external handle is cast copper-free aluminum alloy (less than 4/10 of 1%).
- Cover bolts are stainless steel.
- Eaton (Cutler Hammer) Type DS Switches.
- Two cast conduit hubs, one top and one bottom.
- Internal disconnect handle mechanism is a sliding plate mounted to the cover.

Specifications

Hazardous Rating(s)	• Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer
Nema Rating	3R, 4, 9(E, F, G)
UL File Number	E53290
CSA File Number	LR11714
Buy America(n) Qualified	Contact Manufacturer

Conductor

Number Of Wires	4
Number Of Poles	3

Current

Primary Voltage	600 VAC/250 VDC
Frequency Rating	60 Hz

Dimensions

Depth	6.875 in
Width	8.75 in
Weight	11 lb.
Height	11.875 in

General

Type	Non-Fused Disconnect
Enclosure Type	Bolted
Series	XEDS Series
Material	Aluminum, Copper Free (less than 4/10 of 1%)
UPC	783936066295
Mounting Type	Wall

Operational

Operating Temperature Celcius Max	40 Degree
-----------------------------------	-----------

Product Assets

[Catalog \[English\]](#)