



XMSW-OCT SU-2 SU-3 - Manual Motor Starter - NEMA Size 0 - 3-Pole; 3Ø, Ac - With Hinge

By Killark
Catalog # XMSW-OCT SU-2 SU-3

Manual Motor Starter - NEMA Size 0 - 3-Pole; 3Ø, Ac - With Hinge

Features

- Rectangular bolted cover design provides for attractive, compact, uniform installations.
- Enclosure and external handle are diecast copper-free (less than 0.4%) aluminum alloy.
- Cast “ON,” “OFF,” “TRIPPED” markings on cover align with external handle and provide clear indication of enclosed starter condition.
- External handle is a vault type with standard provisions for locking in the “OFF” position with up to three pad-locks.
- Provision for locking in “ON” position is available as factory modification (add suffix SU-40 to catalog number).
- Two cast 1” NPT conduit hubs with integral pipe stop, one top and one bottom, are standard on all assemblies.
- Supplied with a drain fitting in the bottom and a breather fitting in the top.
- Includes hinges.

Specifications

- | | |
|---------------------|--|
| Hazardous Rating(s) | <ul style="list-style-type: none"> • Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA |
|---------------------|--|



- Class II, Divisions 1 & 2, Groups E, F, G
 - Class III, Divisions 1 & 2
- Contact Manufacturer
E12379
Contact Manufacturer

EU RoHS Indicator
UL File Number
Buy America(n) Qualified

Current

Voltage Rating 600 V

Dimensions

Size 0

General

Series	XMSW Series
UPC	783936912615

Operational

Horsepower - Maximum 5

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)