



# XMSW-DBT SU-3 - Manual Motor Starter - NEMA Size 1-1/2 - 3-Pole; 3Ø, Ac

By Killark  
Catalog # [XMSW-DBT SU-3](#)

Manual Motor Starter - NEMA Size 1-1/2 - 3-Pole; 3Ø, Ac



## Features

- Rectangular bolted cover design provides for attractive, compact, uniform installations.
- Enclosure and external handle are diecast copper-free (less than 0.4%) aluminum alloy.
- Cast “ON,” “OFF,” “TRIPPED” markings on cover align with external handle and provide clear indication of enclosed starter condition.
- External handle is a vault type with standard provisions for locking in the “OFF” position with up to three pad-locks.
- Provision for locking in “ON” position is available as factory modification (add suffix SU-40 to catalog number).
- Two cast 1” NPT conduit hubs with integral pipe stop, one top and one bottom, are standard on all assemblies.
- Supplied with a drain fitting in the bottom and a breather fitting in the top.

## Specifications

- Hazardous Rating(s)
- Class I, Divisions 1 & 2, Groups C, D
  - Class I, Zones 1 & 2, Groups IIB, IIA

- Class II, Divisions 1 & 2, Groups E, F, G
  - Class III, Divisions 1 & 2
- Contact Manufacturer  
E12379  
Contact Manufacturer

EU RoHS Indicator  
UL File Number  
Buy America(n) Qualified

## Current

Voltage Rating 600 V

## Dimensions

Size 1.5

## General

Series XMSW Series  
UPC 783936913032

## Operational

Horsepower - Maximum 5

## Product Assets

- [Catalog \[English\]](#)  
[Catalog Page \[English\]](#)