



XS Series 2-Pole Tumbler Switch Cover Without Device - 20A

By Killark
Catalog # [XNS-2C](#)

XS Series - Aluminum 2-Pole Tumbler Switch Cover Without Device - 20A



Features

- Front lever rotary operated switch assemblies.
- Standard provisions for padlocking in either “ON” or “OFF” position.
- The lever is connected to a threaded stainless steel shaft which passes through the cover.

Application

Used where making, breaking, or changing connections in an electric circuit is required.

Specifications

UL File Number	E53360
Buy America(n) Qualified	Contact Manufacturer
CSA File Number	LR11712
Hazardous Rating(s)	• Class I, Divisions 1 & 2, Groups C, D • Class I, Zones 1 & 2, Groups IIB, IIA • Class II, Divisions 1 & 2, Groups E, F, G • Class III, Divisions 1 & 2
EU RoHS Indicator	Contact Manufacturer

Conductor

Number Of Poles	2
-----------------	---

Configuration

Back Box Type	SWB
Current	
Frequency Rating	50/60 Hz
Amperage Rating	20 A
Dimensions	
Height	3.25 in
Width	5.25 in
Length	5.5 in
Gross Weight with Packaging	0.95
Depth	4-1/4 in
Dimensions	5.5 in x 5.25 in x 3.25 in
General	
Color	Gray
UPC	783936913377
Type	Aluminum Tumbler Switch Cover
Material	Aluminum, Copper Free (less than 4/10 of 1%)
Series	XNS Series
Operational	
Actuator	Lever
Action	DPST

Product Assets

[Catalog \[English\]](#)