



TUMBLER SWITCH



XS-3C



Complete Unit When Assembled

Class I, Div. 1 & 2, Groups C, D
 Class I, Zones 1 & 2, Groups IIB, IIA
 Class II, Div. 1 & 2, Groups E, F, G
 Class III
 NEMA 7 (C, D) 9 (E, F, G)



LISTED - FILE E53360



Certified - File LR11712



File OP7A5.AE

See files for details or call Killark.

FEATURES-SPECIFICATIONS

Applications

Used where making, breaking, or changing connections in an electric circuit are required.

Features

XS and XST Series are front lever rotary operated switch assemblies with standard provisions for padlocking in either "ON" or "OFF" position. The lever is connected to a threaded stainless steel shaft which passes through the cover.

XS TUMBLER SWITCH						
CATALOG NUMBER					SWITCH STYLE	SWITCH RATING 120/277 VAC, 1Ø
COVER		HUB SIZE	COMPLETE UNITS (BOX, COVER AND SWITCH)			
WITH DEVICE	WITHOUT DEVICE		DEAD-END	FEED-THRU		
XS-1C	XNS-1C	1/2"	XS-11C	XS-41C	1-POLE	20AⓈ
		3/4"	XS-21C	XS-51C		
XS-2C	XNS-2C	1/2"	XS-12C	XS-42C	2-POLE	20AⓈ
		3/4"	XS-22C	XS-52C		
XS-8C	XNS-8C	1/2"	XS-18C	XS-48C	3-POLE	①
		3/4"	XS-28C	XS-58C		
XS-3C	XNS-3C	1/2"	XS-13C	XS-43C	3-WAY/ SPDT No center off	20AⓈ
		3/4"	XS-23C	XS-53C		
XS-5C	XNS-5C	1/2"	XS-15C	XS-45C	SPDT Center off	20AⓈ
		3/4"	XS-25C	XS-55C		
XS-6C	XNS-6C	1/2"	XS-16C	XS-46C	DPDT No center off	20AⓈ
		3/4"	XS-26C	XS-56C		
XS-7C	XNS-7C	1/2"	XS-17C	XS-47C	DPDT Center off	20AⓈ
		3/4"	XS-27C	XS-57C		
XS-1D	XNS-1D	1/2"	XS-11D	XS-41D	1-POLE	30AⓈ
		3/4"	XS-21D	XS-51D		
XS-2D	XNS-2D	1/2"	XS-12D	XS-42D	2-POLE	30AⓈ
		3/4"	XS-22D	XS-52D		
XS-4C	—	—	—	—	4-WAY	20AⓈ

① Rated 15 amperes, 240/480 VAC., 3Ø: 3HP-240 VAC., 5 HP-480 VAC.

Ⓢ Horsepower rated 1 HP at 120VAC, 2 HP at 240VAC.



Certified - File LR11712

XS TUMBLER SWITCH				
HUB SIZE	CATALOG NUMBER		SWITCH STYLE	SWITCH RATING 347 VAC, 1Ø
	COMPLETE UNITS (BOX, COVER AND SWITCH)			
	DEAD-END	FEED-THRU		
3/4"	XST15-21C	XST15-51C	1-POLE	15A
1"	XST15-31C	XST15-61C		
3/4"	XST20-21C	XST20-51C	1-POLE	20A
1"	XST20-31C	XST20-61C		
3/4"	XST15-23C	XST15-53C	3-WAY/SPDT NO CENTER OFF	15A
1"	XST15-33C	XST15-63C		
3/4"	XST20-23C	XST20-53C	3-WAY/SPDT NO COVER OFF	20A
1"	XST20-33C	XST20-63C		