



ZN210CR-EX-MG - 3/4" Nylon Cord Connector, 90° w/ Mesh Grip, Cord Range .625-.750, Yellow

By Killark
Catalog # [ZN210CR-EX-MG](#)

3/4" Nylon Cord Connector, 90° w/ Mesh Grip, Cord Range .625-.750, Yellow

Features

- Nylon retention ring for increased holding power
- Neoprene bushing seals against moisture
- Nylon connectors obtain approximately the same retention values as metal cord connectors
- Stainless steel mesh grips resist corrosion, prevent cord pull-out and control arc-of-bend

Application

Durable nylon construction makes these connectors perfectly suited to corrosive environments. Typical applications for nylon cord connectors include food processing facilities, chemical and sewage treatment plants, and off-shore and dockside installations

Specifications

Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
EU RoHS Indicator	Contact Manufacturer
UL File Number	E22698
CSA File Number	LR73478
Buy America(n) Qualified	Contact Manufacturer



Conductor

Cable Range	.625 - .750 in
-------------	----------------

Dimensions

Gross Weight with Packaging	0.15
Hub Size	3/4"
Width	1 in
Height	3 in
Length	2 in
Dimensions	2 in x 1 in x 3 in

General

Type	90° Cord Connector With Mesh Grip
Series	Z-EX Series
Material	Nylon
Finish Type	Natural
Cord Range	.625-.750,
UPC	783936996677
Color Code	Yellow
Color	Black, Gray

Product Assets

[Catalog \[English\]](#)