



ZN210CR-EX - 3/4"Nylon Cord Connector, 90° Bend, Cord Range .625-.750, Yellow

By Killark
Catalog # [ZN210CR-EX](#)

3/4"Nylon Cord Connector, 90° Bend, Cord Range .625-.750, Yellow

Features

- Nylon retention ring for increased holding power
- Neoprene bushing seals against moisture
- Nylon connectors obtain approximately the same retention values as metal cord connectors

Application

Durable nylon construction makes these connectors perfectly suited to corrosive environments. Typical applications for nylon cord connectors include food processing facilities, chemical and sewage treatment plants, and off-shore and dockside installations

Specifications

EU RoHS Indicator	Contact Manufacturer
CSA File Number	LR73478
Hazardous Rating(s)	Suitable for use in hazardous location applications when installed according to NEC Articles 501.10(b) (Class I, Division 2) or 502.10, 503.10, and 505.15 (Class I Zone 2).
UL File Number	E22698
Buy America(n) Qualified	Contact Manufacturer

Conductor



Cable Range	.625 - .750 in
-------------	----------------

Dimensions

Hub Size	3/4"
Length	2 in
Gross Weight with Packaging	0.5
Width	1 in
Height	3 in
Dimensions	2 in x 1 in x 3 in

General

Series	Z-EX Series
Cord Range	.625-.750,
Color Code	Yellow
Color	Gray
Type	90° Cord Connector
Material	Nylon
Finish Type	Natural
UPC	783936972954

Logistics

Carton Quantity	15
-----------------	----

Product Assets

[Catalog \[English\]](#)