



ZN210ZP - 3/4" Steel (Zinc Plated) 90° Cord Connector, Cord Range .625-.750, Yellow

By Killark
Catalog # [ZN210ZP](#)

3/4" Steel (Zinc Plated) 90° Cord Connector, Cord Range .625-.750, Yellow

Features

- Neoprene grommet seals out oil and moisture
- Nylon retention ring incorporates a splithinge design to prevent friction and provide strain relief, also color-coded for sizing identification
- These heavy-duty connectors hold up to most manufacturing chemicals including, acid solutions, solvents and other corrosive materials
- Machined steel nut, malleable iron body allows for tightening the compression nut and NPT hub without worrying about stripping the threads

Specifications

EU RoHS Indicator	Contact Manufacturer
Nema Rating	4, 4X, 12, 13
UL File Number	E22698
CSA File Number	LR73478
Buy America(n) Qualified	Contact Manufacturer

Conductor

Cable Range	.625 - .750 in
-------------	----------------



Dimensions

Gross Weight with Packaging	0.55
Hub Size	3/4"
Width	0.56 in
Height	2.9 in
Length	1.88 in
Dimensions	1.88 in x 0.56 in x 2.9 in

General

Type	90° Cord Connector
Series	Z Series
Material	Steel
UPC	783936121024
Color	Silver

Logistics

Carton Quantity	15
-----------------	----

Product Assets

[Catalog \[English\]](#)