



## Insulated Crimping and Cutting Tool



The Klein Tools Insulated Crimping/Cutting Tool crimps wire from 10 to 22 AWG. This crimper/cutter features a tapered nose for working in confined spaces. Additionally, it features bright orange outer coating on the handles that is flame retardant and impact resistant.

### Specifications

<b>Application:</b>	10-22 AWG Insulated and Non-Insulated Solderless Terminals and Connectors	<b>Special Features:</b>	Flame Retardant and Impact Resistant Handle
<b>Material:</b>	Induction Hardened Steel	<b>Insulated:</b>	Yes
<b>Joint Type:</b>	Hot-Riveted	<b>Nose Type:</b>	Tapered
<b>Cutting Capacity:</b>	10-22 AWG Insulated and Non-Insulated Terminals	<b>Crimping Capacity:</b>	10-22 AWG Insulated and Non-Insulated Terminals
<b>Crimps:</b>	Yes	<b>Standard:</b>	IEC 60900 and ASTM F1505
<b>Handle Color:</b>	Orange	<b>Handle Finish:</b>	2-Layer Insulation
<b>Handle Material:</b>	High-Dielectric Plastic Cushion Grip	<b>Overall Length (Inch):</b>	10
<b>Overall Length (cm):</b>	25.4	<b>Weight (oz):</b>	16
<b>Weight (g):</b>	454		