



Wire Stripper/Cutter 8-16 AWG Stranded



This compact, lightweight wire-stripping, cutting tool cuts, strips, loops and gauges solid wire. Dual layer orange-over-white insulation protects against electric shock. Meets or exceeds ASTM F1505-10, IEC 60900: 2004, CAN/ULC-60900-09, NFPA 70E, 2011 ed., CSA Z462 standards for insulated tools, and are clearly marked with the official 1000-volt rating symbol. Hardened spring steel with precision-ground stripping holes for easy removal of insulation.

Specifications

Application:	8, 10, 12, 14, 16 Stranded AWG	Special Features:	Compact and Lightweight, Spring Loaded For Self Opening
Material:	Steel	Insulated:	Yes
Strips and Cuts:	8-16 AWG Stranded	Standard:	IEC 60900 and ASTM F1505
Overall Length (Inch):	7	Overall Length (cm):	17.8
Handle Color:	Orange	Handle Finish:	2-Layer Insulation
Weight (oz):	9.6	Weight (g):	272