



Insulated Universal Combination Pliers, 8-Inch



Be protected from up to 1,000 volts of electric current when working near energized sources with Klein's 8-Inch Insulated Universal Combination Pliers. These pliers offer flame-retardant handles, a toothed pipe grip and a high-leverage design, with the rivet closer to the cutting edge for 40% greater cutting and gripping power than other pliers designs. The durable, molded insulation meets or exceeds IEC 60900 and ASTM F1505 standards for insulated tools.

Specifications

Type:	High-Leverage Pliers	Application:	Cuts ACSR, Screws, Nails and Most Hardened Wires
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length (Inch):	8.76
Overall Length (cm):	22.3	Material:	Induction Hardened Steel
Nose Type:	Universal	Jaw Length (Inch):	1.78
Jaw Length (cm):	4.5	Jaw Width (Inch):	1.02
Jaw Width (cm):	2.6	Jaw Thickness (Inch):	0.55
Jaw Thickness (cm):	1.4	Knife Length (Inch):	0.711
Knife Length (cm):	1.8	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer Insulation	Handle Length (Inch):	4.93
Handle Length (cm):	12.5	Insulated:	Yes
Standards:	IEC 60900 and ASTM F1505	Weight (oz):	16
Weight (g):	454		