



Grip for High Strength Cables 0.55-Inch



Designed for use on aluminum, copper, weatherproof coated wire, PVC covered conductors and messenger and guy strand. The Chicago style grip was designed for cable sizes from 0.218-Inch to 0.55-Inch (5.5 to 13.9 mm). Double V grooves give four-point contact, reducing chance of slipping and providing proper alignment of wire and cable.

Specifications

Type:	Chicago Grip	Application:	Wire Pulling
Overall Length (Inch):	13.3	Overall Length (cm):	33.8
Overall Height (Inch):	2.5	Overall Height (cm):	6.4
Overall Width (Inch):	7.6	Overall Width (cm):	19.3
Material:	Steel	Cable Type:	Aircraft, EHS, Messenger, Guy Strand
Cable Diameter:	0.218" to 0.55" (5.54 to 13.97 mm)	Hot Latch:	No
Swing Latch:	No	Spring:	Yes
Locking Handle:	Yes	Jaw Type:	Double V
Teeth Type:	Smooth	Jaw Length (Inch):	5
Jaw Length (cm):	12.7	Maximum Safe Load (lb):	8000
Maximum Safe Load (kg):	3628.7	Weight (lb):	5.8
Weight (kg):	2.6		