



Parallel Jaw Grip 2-1/2-Inch Length



Lightweight, compact grips pull an exceptionally wide range of cable sizes and types. Designed with a round inside-jaw contour for maximum contact to minimize conductor damage. Lower jaw is serrated to firmly grip insulated cables and conductors. Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable.

Specifications

Type:	Parallel Jaw Grip	Application:	Wire Pulling
Special Features:	Spring	Overall Length (Inch):	9.52
Overall Length (cm):	24.2	Overall Height (Inch):	5.31
Overall Height (cm):	13.5	Overall Width (Inch):	1.22
Overall Width (cm):	3.1	Material:	Steel
Cable Type:	Messenger, EHS, Coated	Cable Diameter:	0.157" to 0.875" (3.98 to 22.22 mm)
Hot Latch:	No	Swing Latch:	No
Spring:	Yes	Locking Handle:	No
Jaw Type:	Round	Teeth Type:	Coarse
Jaw Length (Inch):	2.5	Jaw Length (cm):	6.4
Maximum Safe Load (lb):	4500	Maximum Safe Load (kg):	2041.2
Weight (lb):	2.6	Weight (kg):	1.2