



Parallel Jaw Grip 4-1/2-Inch Length



Lightweight, compact grips pull an exceptionally wide range of cable sizes and types. Designed with a round inside-jaw contour for maximum contact to minimize conductor damage. Lower jaw is serrated to firmly grip insulated cables and conductors. Design includes a latch that prevents the grip from falling in case of jaw disengagement from the cable.

Specifications

Type:	Parallel Jaw Grip	Application:	Wire Pulling
Special Features:	Hot Latch, Spring	Overall Length (Inch):	11.7
Overall Length (cm):	29.7	Overall Height (Inch):	6.4
Overall Height (cm):	16.3	Overall Width (Inch):	2.4
Overall Width (cm):	6.1	Material:	Steel
Cable Type:	Messenger, EHS, Guy Strand	Cable Diameter:	0.625" to 1.25" (15.87 to 31.75 mm)
Hot Latch:	Yes	Swing Latch:	No
Spring:	Yes	Locking Handle:	No
Jaw Type:	Round	Teeth Type:	Coarse
Jaw Length (Inch):	4.5	Jaw Length (cm):	11.4
Maximum Safe Load (lb):	7500	Maximum Safe Load (kg):	3401.9
Weight (lb):	4.8	Weight (kg):	2.2