



Ironworker's Pliers, Aggressive Knurl, 9-Inch



Klein Tools Ironworker's Pliers have aggressive teeth for a strong grip when twisting, snipping and pulling soft annealed rebar tire wire. The knurled jaws aid in easy twisting and turning. These pliers feature a hook-bend in the handle for added grip and leverage. Unique handle tempering helps absorb the "snap" when cutting wire.

Specifications

Type:	Ironworker's Pliers	Application:	Used for Rebar, High Leverage
Special Features:	Spring Loaded	Overall Length (Inch):	9.29
Overall Length (cm):	23.6	Overall Width (Inch):	2.06
Overall Width (cm):	5.2	Material:	Induction Hardened Steel
Nose Type:	Square	Jaw Length (Inch):	1.91
Jaw Length (cm):	4.9	Jaw Width (Inch):	1.24
Jaw Width (cm):	3.1	Jaw Thickness (Inch):	0.62
Jaw Thickness (cm):	1.6	Jaw Capacity (Inch):	1.375
Jaw Capacity (cm):	3.5	Cutting Knives:	1
Knife Length (Inch):	0.781	Knife Length (cm):	2
Cut Style:	Side-Cutting	Screw Shearing:	No
Joint Type:	Hot-Riveted	Handle Color:	Black
Handle Finish:	Plain	Handle Length (Inch):	7.375
Handle Length (cm):	18.7	Insulated:	No
Tether Capable:	No	Weight (oz):	16
Weight (g):	454		